

# LUVOCOM® 3F PPS GF 50300 BK

Polyphenylene sulfide, linear  
with glass fibers and mineral filler, black

Physical properties		Test method	Specimen	Units	Typical value
Specific gravity		ISO 1183		g/cm <sup>3</sup>	1,65
Water absorption	23°C / 24h	ISO 62	ISO 3167 A	%	<0,05
Melt volume rate (MVR)		316 °C / 1,27kg	pellet	cm <sup>3</sup> /10 min	12
Flammability behaviour		UL 94	1/16"		(V-0)

Mechanical properties at 23°C / 50% rh					
Tensile strength	dry, @50 mm/min	ISO 527	ISO 3167 A	MPa	126
Elongation @Fmax.	dry, @50 mm/min	ISO 527	ISO 3167 A	%	1,4
Tensile modulus	dry, @1 mm/min	ISO 527	ISO 3167 A	GPa	11
Impact strength	dry	ISO 179 1eU	80x10x4mm	kJ/m <sup>2</sup>	30

Thermal properties					
Continuous service temp.	20.000 h	IEC 60216	ISO 3167 A	°C	220
Service temperature	during lifetime max. 200h		ISO 3167 A	°C	240

Electrical properties					
Insulation resistance	strip electrode R25	DIN EN 62631-3-3	ISO 3167 A	Ω	≥10 <sup>9</sup>
Surface resistance	ROB	DIN EN 62631-3-2	Ronde 60x4mm	Ω	≥10 <sup>9</sup>

## Main features

High continuous-use and heat-distortion temperatures. Non flammable. Highly chemically-resistant parts. Isotropic shrinkage characteristics.

# LUVOCOM® 3F PPS GF 50300 BK

Polyphenylene sulfide, linear  
with glass fibers and mineral filler, black

## Recommended processing parameters

### General

3D Printing parameters may vary from machine to machine. The following settings may be used as an indication: nozzle temperature: 310 - 340 °C / nozzle material: abrasion resistant / print bed temperature: > 50 °C / layer thickness: > 0,2mm / printing speed 40 - 60 mm/s.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

### Delivery form & storage

Unless indicated otherwise, the material is delivered as 3mm long pellets in sealed bags on pallets. Preferably storage should be effected in dry and normally temperatured rooms.

### Predrying

It is advisable to predry the granules with a suitable dryer immediately before processing. The granule may absorb moisture from the environment.

Dryer type	Temperature °C	Drying time in h
Dehumidifying dryer	100 - 140	2 - 4
Vacuum Dryer	50 - 90	> 4

### Recommended processing parameters

In general LUVOCOM® 3F can be processed on conventional extrusion machines while observing the usual technical guidelines. Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder, screw and die should be protected against wear as is usual in the processing of reinforced thermoplastic materials. Lengthy dwell times for the melts in the cylinder should be avoided. Lower the temperatures during interruptions!

Melt temperature	Nozzle	Zone 3	Zone 2	Zone 1
330 °C	320 - 340 °C	320 - 340 °C	310 - 330 °C	300 - 320 °C

### Additional information

Filaments produced from this material may be wound into standard size spools.

50300 01 03 21

#### Europe and Head Office

Lehmann&Voss&Co. KG  
Alsterufer 19  
20354 Hamburg  
Germany  
Tel +49 40 44 197-0  
Email: [luvocom@ehvoss.de](mailto:luvocom@ehvoss.de)

#### North America

LEHVOSS North America Inc.  
185 South Broad Street  
Pawcatuck, CT 06379  
USA  
Tel +1-855-681-3226  
Email: [info@lehvoss.us](mailto:info@lehvoss.us)

#### Asia

LEHVOSS (Shanghai) Chemical Trading Co., Ltd.  
Unit 4805, 8 Xingyi Road  
Changning District, Shanghai 200336  
China  
Tel +86 21 62785181  
Email: [info@ehvoss.cn](mailto:info@ehvoss.cn)

