

# LUVOCOM® 3F PP CF 9928 BK

Polypropylene-copolymer  
with carbon fibers, black

Physical properties		Test method	Specimen	Units	Typical value
Specific gravity		ISO 1183		g/cm <sup>3</sup>	1,00
Water absorption	23°C / 24h	ISO 62	ISO 3167 A	%	<0,3
Linear mould shrinkage		DIN 16742	ISO 3167 A	%	0,2-0,6

Mechanical properties at 23°C / 50% rh					
Tensile strength	dry, @50 mm/min	ISO 527	ISO 3167 A	MPa	92
Elongation @Fmax.	dry, @50 mm/min	ISO 527	ISO 3167 A	%	2,5
Tensile modulus	dry, @1 mm/min	ISO 527	ISO 3167 A	GPa	9,5
Flexural strength	dry, @10 mm/min	ISO 178	ISO 3167 A	MPa	90
Flexural elongation @Fmax.	dry, @10 mm/min	ISO 178	ISO 3167 A	%	2,2
Flexural modulus	dry, @2 mm/min	ISO 178	ISO 3167 A	GPa	7
Impact strength	dry	ISO 179 1eU	80x10x4mm	kJ/m <sup>2</sup>	42

Thermal properties					
Vicat softening temp.	VST A	DIN ISO 306	ISO 3167 A	°C	80
Continuous service temp.	20.000 h	IEC 60216	ISO 3167 A	°C	100
Service temperature	during lifetime max. 200h		ISO 3167 A	°C	130

Electrical properties					
Insulation resistance	strip electrode R25	DIN EN 62631-3-3	ISO 3167 A	Ω	10 <sup>17</sup>
Surface resistance	ROB	DIN EN 62631-3-2	Ronde 60x4mm	Ω	≤10 <sup>7</sup>

## Main features

Strong, stiff parts. Electrically conductive, suitable for continuous discharging of statically-generated electricity. Low warpage.

## Recommended processing parameters

### General

3D Printing parameters may vary from machine to machine. The following settings may be used as an indication: nozzle temperature: 220 - 250 °C / nozzle material: abrasion resistant / print bed temperature: > 50 °C / layer thickness: > 0,2mm / printing speed 40 - 60 mm/s.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

### Delivery form & storage

Unless indicated otherwise, the material is delivered as 3mm long pellets in sealed bags on pallets. Preferably storage should be effected in dry and normally temperatured rooms.

# LUVOCOM® 3F PP CF 9928 BK

Polypropylene-copolymer  
with carbon fibers, black

## Predrying

It is advisable to predry the granules with a suitable dryer immediately before processing. The granule may absorb moisture from the environment.

Dryer type	Temperature °C	Drying time in h
Dehumidifying dryer	70 - 95	2 - 4

## Recommended processing parameters

In general LUVOCOM® 3F can be processed on conventional extrusion machines while observing the usual technical guidelines. Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder, screw and die should be protected against wear as is usual in the processing of reinforced thermoplastic materials. Lengthy dwell times for the melts in the cylinder should be avoided. Lower the temperatures during interruptions!

Mold	Melt temperature	Nozzle	Zone 3	Zone 2	Zone 1
40 - 80 °C	60 °C	220 - 250 °C	230 - 260 °C	220 - 250 °C	220 - 250 °C

## Additional information

During processing, the moisture content should not exceed 0.2%. Moisture may lead to smearing and in extreme cases to foaming. Usually the material can be processed over a broad temperature range and can thus be adapted to a wide variety of processing conditions. The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

09928 30 07 18

### Europe and Head Office

Lehmann&Voss&Co. KG  
Alsterufer 19  
20354 Hamburg  
Germany  
Tel +49 40 44 197-0  
Email: [luvocom@ehvoss.de](mailto:luvocom@ehvoss.de)

### North America

LEHVOSS North America Inc.  
185 South Broad Street  
Pawcatuck, CT 06379  
USA  
Tel +1-855-681-3226  
Email: [info@lehvoss.us](mailto:info@lehvoss.us)

### Asia

LEHVOSS (Shanghai) Chemical Trading Co., Ltd.  
Unit 4805, 8 Xingyi Road  
Changning District, Shanghai 200336  
China  
Tel +86 21 62785181  
Email: [info@lehvoss.cn](mailto:info@lehvoss.cn)

